

Reel-in-Box cable solution



FEATURES

- **Compact dimensions:**
13" x 11" x 13.5" (D x W x H)
- **Wide-mouth opening:** Enable easy and controlled spooling and re-reeling
- **Limited “free spin reel”:** Reduce cable waste and improve handling
- **Weatherized-resistant design:** Protect from outdoor elements for reliable performance
- **Dual carry handles:** Simplify transport and mobility
- **3-stage tension adjustment:**
Customize control from low to high
- **Sustainable construction:** Use recycled material for sustainability

Smart, portable cable management

CommScope’s Reel-in-Box cabling solution streamlines fiber installation by eliminating the need for reels, stands, or specialized equipment—just place the box and pull. Its compact, stackable design supports multiple cable runs, saving time on setup and transport. The durable weatherized packaging protects cable integrity and prevents tangling, allowing installers to work efficiently without extra hands.

Commscope’s Reel-in-Box holds 1000 ft of 4.25 mm single fiber cable to serve a variety of applications. The extra-wide opening facilitates easier cable disbursement and routing throughout the dwelling. With three stages of adjustable tension, installers can choose how quickly to dispense the cable for the job at hand.

Catalog number	Description key	Cable diameter	Weight with cable in box	Cable length	Color	Quantity
House Wrap Reel-in-Box						
810009223/DB	R-001-DN-8G-F01BK/SP18/RNB	4.2 mm	26 lbs	1000 ft	Black	27 boxes/27K ft
810009224/DB	R-001-DN-8GF01WH/SP18/RNB	4.2 mm	26 lbs	1000 ft	White	27 boxes/27K ft
RealFlex® 3 Reel-in-Box						
900003177/DB	R-001-SP-8GF29IV/WB/RNB	2.9 mm	10 lbs	1000 ft	Ivory	27 boxes/27K ft
4.9 mm Fiber Drop Cable Reel-in-Box						
810009230/DB	R-001-DN-8G1-F49IV/SP29/RNB	4.9 mm	20 lbs	1000 ft	Ivory	27 boxes/27K ft
810009267/DB	R-001-DN-8G1-F49BK/SP29/RNB	4.9 mm	20 lbs	1000 ft	Black	27 boxes/27K ft
810009268/DB	R-001-DN-8G1-F49WH/SP29/RNB	4.9 mm	20 lbs	1000 ft	White	27 boxes/27K ft

Eco-friendly design meets field-ready performance

- Compact design
- Convenient carry handles
- Durable, eco-friendly packaging
- 3-stage reel braking knob



Wide-mouth opening for easy cable deployment

Engineering the future of broadband™

Service providers across North America trust CommScope for complete, end-to-end Fiber-to-the-Home (FTTH) solutions that optimize broadband deployments with reliable quality. Our proven, innovative technologies help deploy faster, simplify management and scale to meet the demands of modern connectivity, advancing Broadband For Everyone™ solutions. Backed by 50 years of U.S.-based expertise and offering [Build America, Buy America \(BABA\)](#)—compliant products tailored to today's standards, CommScope empowers providers to deliver future-ready networks while maximizing cost efficiency and supporting long-term value.

Discover more at commscope.com.

COMMScope®

commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2025 CommScope, LLC. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see, <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners.

CO-1205281-EN (11/25)