COMMSCOPE°



BUDI Connectorized with FIST

Building Distribution Enclosure for Connectorized Applications

What is BUDI?

BUDI is a product range of compact, wall mountable fiber enclosures for indoor and outdoor use. They are specifically designed for fast deployment and easy customer connection. The FIST management system is a proven CommScope technology for optimal fiber organization and splicing. In combination with a patch panel, this system offers ultimate flexibility.

Available with splicing and/or patching capabilities, high connector density, small and larger footprints, the BUDI product range offers flexible solutions for a wide range of applications in the access network

Benefits

- Easy to install
- Compact and flexible design
- Fast customer connection
- Extensive product range
- Proven FIST fiber management system

Features

- Designed to operate in category C (controlled), category G (outdoor ground level) and category A (aerial) as characterized by IEC 61753-1
- Fire retardant, LSZH materials
- UV stable material for outdoor above ground use
- Multiple cable ports available
- Bottom cable seal blocks are wraparound
- UMS (Universal Mounting System) available to mount single element/single circuit trays splice trays
- Compatible with pre-connectorized Mini-Breakout cable
- Allows integration of passive optical components
- Small and large footprints
- Multiple accessories available to terminate and seal different cable types
- Removable enclosure lid
- Quareo Scan Assist compatible

BUDI Connectorized with FIST Building Distribution Enclosure for Connectorized Applications

г.,		Type of BUDI					
Features		BUDI-2S-T	BUDI-1S-T	BUDI-S-T	BUDI-M-TP	BUDI-M-TA	
UMS		2	8	24	24	24	
Ports	SC	8	16	24	36	48	
	LC	12	32	48	72	64	
Splices	Single circuit (up to 2 splices per tray)	12	16	48	48	48	
	Single element (up to 12 splices per tray)	36	48	144	144	144	
Cable loop		no	yes	yes	yes	yes	
Lock		lead wire	key	key	key	key	
FSASA splitter integration		no	yes	yes	yes	yes	
Quareo Scan Assist compatibility		yes	yes	yes	yes	yes	

Dimensions





Size	BUDI-2S	BUDI-1S	BUDI-S	BUDI-M
A: Height box (mm)	260	340	425	480
B: Height cover (mm)	285	420	500	550
C: Width (mm)	155	240	295	360
D: Depth (mm)	60	120	145	175



Building Distribution Enclosure for Connectorized Applications

Ordering Information

Pre-configured box

BUDI-2S-T-XX XX E S								
Number of adapters and pigtails*			Type of adapter and pigtail					
02	SC/LC			S1	SC/UCP			
04	SC/LC			S2	SC/APC 8°			
06	SC/LC			L1	LC/UPC			
08	SC/LC			L2	LC/APC			
12	LC only							

* Pigtails and adapters are included in the packaging but not pre-installed in the product

Pre-configured box



* Pigtails and adapters are included in the packaging but not pre-installed in the product



Building Distribution Enclosure for Connectorized Applications

Pre-configured box





Building Distribution Enclosure for Connectorized Applications

Pre-configured box



Accessory required for BUDI-M-TA



Building Distribution Enclosure for Connectorized Applications

Empty boxes



* Only sliding adapter pack holders included.



commscope.com

Visit our website or contact your local CommScope representative for more information.

© 2016 CommScope, Inc. All rights reserved.

BUDI, SMOUV and all trademarks identified by ® or ™ are registered trademarks or trademarks, respectively, of CommScope, Inc. This document is for planning purposes only and is not intended to modify or supplement any specifications or warranties relating to CommScope products or services. PS-318900.3-EU (06/16)