



DATA CENTER

# Rapid Fiber Connect™ platform

**Engineered for AI. Built for Scale.**

First Edition

**COMMSCOPE®**  
an Amphenol company


# The Rapid Fiber Connect™ platform solves ultra-dense AI complexity with plug-and-play simplicity

Exploding AI demand is driving the need for more ultra-dense GPU racks, pods, and clusters — requiring tens of thousands fiber connections. The resulting time, complexity and risk associated with these deployments create major challenges for data center operators, designers and integrators.

CommScope's Rapid Fiber Connect solution is a rack-scale, plug-and-play platform, purpose-built for ultra-dense AI data centers. It simplifies cabling, testing, deployment and scaling through flexible panel designs and integrated, pre-configured, pre-labeled pigtailed that allow for GPU and switch connections to be made and integrated off site. On site, Mass Insert connectors accelerate installation and system turn-up with fewer connections.

## The result

- Simplified and faster cabling that helps reduce mistakes
- Easier off-site validation testing
- Reduced labor skill requirements on site
- Higher fiber density with fewer connection "clicks" required on site
- Streamlined upgrades for scaling AI environments



# Four ways

## Rapid Fiber Connect rack-scale, plug-and-play platform empowers AI data center evolution:



1

### Accelerated deployment

Pre-configured, pre-labeled and factory terminated pigtail outputs reduce rack assembly time and opportunity for error. The panel accepts Mass Insert connectors, allowing rack-to-rack connectivity with 12 times fewer clicks than required by individual MPO12/8 connectors. Trunk cables can also be deployed on site prior to roll in for even faster deployments.



2

### Optimized for AI architectures

The platform aligns with modern AI reference designs, offering flexible panel options, optimized connector layouts, and integrated spare capacity. Its optimized panel port counts, locations and types support various trunk and patching fiber counts. Its integrated spare panel ports enable the repair of broken links without pulling new cable. Multimode and singlemode solutions are available.



3

### Ultra-high density

The Rapid Fiber Connect platform features a 1RU front access panel with a maximum density of 960 fibers to connect GPUs and CPUs in common 72-GPU rack-scale systems. Its 1RU front and rear panels support up to 1,728 fibers. Mass Insert connectors deliver 12 times density over MPO12/8, and the solution is stackable to service ultra-high density switch racks.



4

### Pre-configured for risk mitigation

Off site configuration reduces on site manual labor, cost, and potential risk by leveraging pre-labeled pigtails and legs configured to align with the rack design. Its front access panel prevents potential mistakes caused by working in deep, overcrowded racks. Once configured, the rack can roll in fully assembled for simplified Mass Insert connection.

# Rapid Fiber Connect platform

Uniquely designed for speed and simplicity, the Rapid Fiber Connect platform consists of GPU and switch panels with pre-installed output cabling and trunk cable terminated with Mass Insert trunk connectors.



## Rapid Fiber Connect GPU panel

The front access only design supports up to 960 fibers and is ideal for high-density racks. It is also optimized for a 72-GPU rack scale system designs.



## Rapid Fiber Connect switch panel

The front and/or rear access switch panel supports up to 1,728-fibers and is stackable to achieve ultra-high fiber density.




## Trunk cables with Mass Insert connector

Trunks are available in singlemode and multimode to connect between racks and across pods, and in various lengths and fiber counts to match specific applications.

## Rapid Fiber Connect panels key features

Feature	Rapid Fiber Connect panel for GPU cabinets	Rapid Fiber Connect panel for switch cabinets
Optimized for	72 GPU rack-scale systems, such as Nvidia NLV72 or AMD Helios racks	Switch cabinets (leaf/spine/core)
Fiber type	Multimode and Singlemode	Multimode (within pod) and Singlemode (between pods)
Rack space	1RU	1RU (can be stacked)
Maximum fiber capacity	960 fibers	1,728 fibers
Access type	Front access only	Front and rear access
Front connection	MPO pigtails for GPU, CPU, spares Mass Insert connectors for trunk cable	MPO pigtail into switches, spares
Rear connections	None	Mass Insert connectors for trunk cable


Trunk cable constructed with Mass Insert connectors to make connection in between racks: available in singlemode and multimode, in different lengths and fiber counts matching the specific application.



Engineered for AI. Built for Scale.


# Typical application examples

## 1. Connecting GPU cabinet to leaf switches inside a pod



- 1 Rapid Fiber Connect GPU panel (all front access) 
- 2 Rapid Fiber Connect multimode trunks with Mass Insert connectors 
- 3 Rapid Fiber Connect switch panel (front + rear access) 
- 4 GPU cabinets—rack-scale systems
- 5 Leaf switch cabinets
- 6 CommScope FiberGuide® fiber raceway

## 2. Connecting AI pods to build out a large AI cluster



- 1 Rapid Fiber Connect Switch panel (front + rear access) 
- 2 Rapid Fiber Connect singlemode trunk cables with Mass Insert connector 
- 3 Spine switch cabinet
- 4 Core switch cabinets
- 5 AI pod composed of GPU cabinets rack-scale systems and leaf switch cabinet

# Ordering Information

## Rapid Fiber Connect Panels

### 1. Rapid Fiber Connect GPU panel

See application example 1, item 1

Note: This scheme details the options that are available to configure a GPU cabinet, front panel (optimized for 72 GPU designs).

Specific configurations required will be released as discrete 760... MIDs.



760...MID Description

RFC	1U	00864	1	X	6X	F	C	QP	F
	Panel RU Size 1U 2U 3U 4U 6U etc	Panel Fiber Count 00432 432 Fibers 00864 864 Fibers 01152 1152 Fibers 01728 1728 Fibers 02304 2304 Fibers 03456 3456 Fibers 06912 6912 Fibers etc etc	Panel Number 1 2 3 4 5 6 etc	Fiber Type G Teraspeed SM, G.657.A2 X LazrSPEED 550MM, OM4	Input Connectors 6X MMC16 MI Pinned 6-port Adapter	Input Side F Front Panel B Back Panel	Input Position L Left Entry R Right Entry C Center S Split Left & Right	Output Connectors QP MPO8 unpinned RP MPO16 unpinned HP MPC8 unpinned UP MMC16 unpinned	Output Position F Front Panel B Back Panel

Note: Exact pigtail lengths can be configured to the network layout need.

### 2. Rapid Fiber Connect switch panel

See application example 2, item 2

Note: This scheme details the options that are available to configure a leaf switch facing spine with 4x 4RU switches with spares.

Specific configurations required will be released as discrete 760... MIDs.



760...MID Description

RFC	2U	03456	2	G	6X	B	C	QP	F
	Panel RU Size 1U 2U 3U 4U 6U etc	Panel Fiber Count 00432 432 Fibers 00864 864 Fibers 01152 1152 Fibers 01728 1728 Fibers 02304 2304 Fibers 03456 3456 Fibers 06912 6912 Fibers etc etc	Panel Number 1 2 3 4 5 6 etc	Fiber Type G Teraspeed SM, G.657.A2 X LazrSPEED 550MM, OM4	Input Connectors 6X MMC16 MI Pinned 6-port Adapter	Input Side F Front Panel B Back Panel	Input Position L Left Entry R Right Entry C Center S Split Left & Right	Output Connectors QP MPO8 unpinned RP MPO16 unpinned HP MPC8 unpinned UP MMC16 unpinned	Output Position F Front Panel B Back Panel

Note: Exact pigtail lengths can be configured to the network layout need.

#### 1RU panel dimensions

Height	Width	Depth
1.7" (4.3 cm)	19.3" (49.0 cm)	34.0" (86.4 cm)

Note: Dimensions will scale as Rapid Fiber Connect panels are stacked.

# Cable assemblies


## 1. Singlemode Trunk connecting leaf > spine

See application example 2, item 2

Note: This scheme details the options that are available for bundled array assemblies.

Specific configurations required will be released as discrete 760... MIDs.

**Design note**  
We recommend bundled arrays for shorter distances, max 100ft /30m; and trunks for the longer distances.




## 2. Bundled Array connecting GPU > leaf switch

See application example 1, item 2

Note: This scheme details the options that are available for bundled array assemblies.

Specific configurations required will be released as discrete 760... MIDs.



**Contact your CommScope representative or our Data Center - Customer Service team to discuss the options available to you with the Rapid Fiber Connect™ platform.**

CommScope pushes the boundaries of communications technology with game-changing ideas and ground-breaking discoveries that spark profound human achievement. We collaborate with our customers and partners to design, create and build the world's most advanced networks. It is our passion and commitment to identify the next opportunity and realize a better tomorrow.

Discover more at [commscope.com](https://commscope.com)



---

[commscope.com](https://commscope.com)

©2026 CommScope Technologies LLC, an Amphenol company. All rights reserved.

CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see <https://www.commscope.com/trademarks>. All product names, trademarks and registered trademarks are property of their respective owners.

CO-120752-EN (03/26)